

PCA320 Integrated Crane Scale



PCA320

Super power saving

High safety and reliability

Steel housing with anti-corrosion coat

Rechargeable battery

Loadcell physical protection

CraneMate



Convenient overhead weighing solution
For legal trade or non-trade situation

METTLER TOLEDO

PCA320 Integrated Crane Scale

High safety, reliability and performance


METTLER TOLEDO PCA320 integrated crane scale represents the latest level of technology and performance in the weighing industry.

Super power saving engine, loadcell physical protection, waterproof, anti-shockprint circuit board, 5 digital 25mm LED display, versatile features and TUV, CE, EC approvals do make it the ideal scale for overhead material weighing and handling in legal trade or non-trade situation.

Its unique features include: a total register for accumulating total weight and number of weighing, 10 preset tare memories and peak hold to capture and hold the highest applied load.

Specifications

Accuracy class	III (EC approved)
Stabilization time	Less than 10 seconds
Remote control distance	8~10m
Readable distance	8~10m
Operating temperature	-10~+50 degree centigrade
Humidity range	Less than 95%
Scale power	6V7Ah lead acid battery
IP class	IP65



Models and Dimensions

Model	Resolution(kg)	Net(kg)	Dimensions(mm)					
			H	B	Ød1	F	Ød2	Ød3
PCA320-0100	0.05	28	632	40	50	97	60	20
PCA320-0250	0.1							
PCA320-0500	0.2							
PCA320-1	0.5							
PCA320-2	1	30	688	40	50	130	90	28
PCA320-3	1	32	726	47	60			
PCA320-5	2	32	726	47	60	130	90	28
PCA320-10	5	60	935	69	85	165	100	36

PCA320 Features

- 5 digital 25mm high brightness LED display
- Steel housing with anticorrosive coat
- Electroplated hook and shackle
- Waterproof construction, enclosure IP65
- Swivel hook keeping weight reading always facing you
- Scale body key board and remote operating
- Power: 6VDC 7Ah lead acid battery, 2 Units, being used in turn and changed easily
- Infraed remote control
- Super power saving, 150 hours continuous use between charging
- Especially suitable to be used in dim or evening shift situation

PCA320 Functions

- Cursors indicating weight unit, data feature and scale situation
- 7 keys and its combination realizing function shift and parameter setting
- Tare, clear, zero, dynamic testing, auto zero maintenance
- 10 tare memories, 10 ID number manual or automatic weight accumulation
- 10 weighing memories
- Power saving mode, automatic sleep and power off overtime static weighing
- Peak hold, high and low preset point output
- Low voltage alarm and automatic power off



Standard equipment

- One Scale Body(including LED display, Loadcell)
- Two Batteries(rechargeable)
- One Charger
- One Remote controller
- One Cart



www.mt.com

For more information

METTLER TOLEDO

Industry/Retail

Add: 111 West Tai Hu Road, Xinbei District,
Changzhou, Jiangsu

Tel: 0519-86642040

Fax: 0519-86641991

E-mail: ad@mt.com

Laboratory/Process/Product Inspection

Add: 589 Gui Ping Road, Shanghai

Tel: 021-64850435

Fax: 021-64853351

E-mail: ad@mt.com

